Cadmix II

Product specifications

Unique 2 in 1 solution forrefreshing SLS powders andtumbling finished prints

- Precise post-processing quickly and effortlessly
- Functional and safe with intuitive control
- Compact and easy to handle
- Clean and automatic mixing and churning process



Refreshing

Saves work and time

one operation instead of threeor more when using classic sieve

Ensures clean process

there is no need forrepeated manipulation, the wholeprocess is automatic

Mix perfectly

precisely prepared SLS powder in few minutes

Works completely safely the whole process takes placein closed chamber with sensorfor immediate stop

Tumblina

Saves work and time

replaces sanding of the prints, and the associated time requirement of the process

Perfect post-process

no part of the print is left unprocessed

Allows the choice of abrasive

for use on other materials as well (metal, wood) depending on the chosen abrasive

Works completely safely

the whole process takes placein closed chamber with sensorfor immediate stop



PACKAGE DIMENSIONS		DIMENSIONS OF THE MACHINE	
50	Height (mm):	727	
30	Width (mm):	416	
30	Depth (mm):	567	
50	Mass (kg):	43	
	Speed range (W):	400	
	Tension (V):	230	
	30 30 50	Height (mm): Width (mm): Depth (mm): Mass (kg): Speed range (W):	

A PART OF THE PACKAGE













Abrasive

Glycerine

SLS 3D print. that you will enjoy!

